



NOTES:

1. For Thread (Table I) or Conduit (Table II) sizes not shown, please consult factory for availability.
2. Dimensions of "B" and "F2" Hex Flats may vary based on "A" Thread and Conduit size ordered. "F2" Hex Flats will be determined by the larger of the two, but no smaller than "F2" specified in Table II.

Metric Dimensions (mm) are indicated in parentheses.

712-460
FIRST Swivel Adapter for Glenair Conduit Fittings
Mates with Series 75 Metal-Core Conduit (750-145 & 750-147)



TABLE I

Dash Number	A Thread Class 2B	B Hex Flats	C + .010
24	3/4-20 UNEF	.875 (22.2)	.505 (12.8)
28	7/8-20 UNEF	1.000 (25.4)	.630 (16.0)
32	1-20 UNEF	1.125 (28.6)	.755 (19.2)
36	1 1/8-18 UNEF	1.250 (31.8)	.880 (22.4)
40	1 1/4-18 UNEF	1.375 (34.9)	1.005 (25.5)
42	1 5/16-18 UNEF	1.438 (36.5)	1.005 (25.5)
48	1 1/2 -18 UEF	1.625 (41.3)	1.193 (30.3)
56	1 3/4-18 UNS	1.938 (49.2)	1.505 (38.2)

TABLE II

Dash Number	E Ref	F1/F2 Hex Flats
16	.500 (12.7)	1.375 (34.9)
24	.750 (19.1)	1.625 (41.3)
32	1.000 (25.4)	2.000 (50.8)
40	1.125 (28.6)	2.250 (57.2)
48	1.500 (38.1)	2.750 (69.9)

TABLE III: MATERIAL AND FINISH

Symbol	Material	Finish
ZN	Aluminum Alloy	Zinc Nickel (500-Hour Salt Spray)
BZN	Brass	
Z21	316 Cres	Passivate

**Mates with
 710-498 & 710-702
 Bulkhead Feed-Thru Adapters
 and Other Glenair
 Adapters and Transitions**

Metric Dimensions (mm) are indicated in parentheses.